

# **Pressure Relief Valve**

# Our iPolymer Pressure Relief Valve (PRV)

is constructed with a 100% pure PTFE Valve Body and Valve Plug. The single O-Ring design allows user selection of EP, FKM (Viton Eq.) or FFKM (Kalrez Eq.) depending on the flowing media.

The iPolymer PRV is factory configured for a 10 psi to 90 psi pressure range.



The relief valve is fully adjustable within this range by simply adjusting the upper Socket Hex Adjustment Screw and locking in place with the associated locking nut.

Our iPolymer Pressure Relief Valve is configured with three Upper Housing and Lower Base options: Polyvinylidene Fluoride ("PVDF"), Polypropylene ("PP") or Anodized Aluminum ("AA") as shown.

#### **Applications**

- Pump Pressure Relief
- Expansion Container Pressure Relief
- Flow Channel Pressure Relief
- Safety Relief from water hammer
- System protection for individual low pressure component in circuit

#### **Features:**

- All Wetted High-Purity Flow Path
- Ideal for Harsh Chemicals
- Fully Adjustable within an 80 psi selected range
- Teflon Coated Spring is isolated from media

### **Options:**


Low Range Specifications are available (3 - 25 psi range).

Call Factory with Special Requests


Temperature Range		
Ambient		
AA	0°C - 150°C	
PVDF	0°C - 100°C	
PP	0°C - 60°C	
Media		
AA	0°C - 150°C	
PVDF	0°C - 100°C	
PP	0°C - 60°C	








PORT	Α	В	С
1/4" Pipe	2.87	0.75	2.55
1/4" Tube	3.44	0.75	2.55
1/4" Flared	4.07	0.75	2.55
3/8" Pipe	2.87	0.75	2.55
3/8" Tube	3.44	0.75	2.55
3/8" Flared	4.09	0.75	2.55
1/2" Pipe	3.25	0.84	2.73
1/2" Tube	3.65	0.84	2.73
1/2" Flared	4.34	0.84	2.73



## **Pressure Relief Valve: ORDERING FORMAT**



- 1. Please email Customer Service at info@ipolymer.com
- 2. Call us for special applications. We can manufacture our Valves with special mounting and interface dimensions.
- 3. Upon request, alternate material selection from those listed will allow for expanding temperature ratings or other performance characteristics.
- 4. Unauthorized disassembly of this product will void the original factory one-year product warranty. For further details please contact your local Distributor or our factory directly.